

FEATURES

- Brass valve body
- Pressure-balancing diaphragm design valve
- One-piece diaphragm cartridge design for ease of maintenance
- Mixing valve cycles from "cold " to "hot "
- Integral diverter mechanism
- High-temperature limit setting for added safety
- Available with or without screwdriver stops
- Designed for showerhead and handshower applications
- 5.0 gal/min (18.9 l/min) maximum flow rate at 45 psi (310.3 kPa)



CODES/STANDARDS APPLICABLE

Specified model meets or exceeds the following:

- ASME A112.18.1/CSA B125.1
- ASSE 1016

P29305

1/2"- 14 NPT OD 5/8" ID
for 1/2" Nom. Copper Tubing
(all Inlet & Outlet Ports)



ROUGHING-IN NOTES

Avoid cross-flow conditions. Do not install a shut-off device on either valve outlet.

SPECIFIED MODEL

Model	Description	Finishes
P29305-00	Pressure-Balancing Valve with Diverter, without screwdriver stops	<input type="checkbox"/> NA
P29305-WS	Pressure-Balancing Valve with Diverter, with screwdriver stops	<input type="checkbox"/> NA

We reserve the right to make revisions without notice in the design of products or in packaging unless this right has specifically been waived at the time the order is accepted.