

Features

- Brass construction.
- Leak-free ceramic disc valve with lifetime warranty.
- Durable Kohler finishes resist corrosion and tarnishing.
- Flexible G1/2" supply hoses for easy installation.
- 212 mm spout reach.
- 2 function pull-down spray.
- Faucet spout swivel 360 degree.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB 18145-2014
- TIS 2067-2552

Installation Notes

Install this product according to the installation guide.



PULL-DOWN KITCHEN FAUCET K-25981T-4



Specified Model

Model	Description	Color/Finishes
K-25981T-4	Atom pull-down kitchen faucet upright handle	CP: Polished Chrome


For a full range of color finishes in your market please contact your local Kohler representative.



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษจากโคโธเลอร์ คงทน เงางาม
- สายน้ำดีขนาด G1/2" ง่ายต่อการติดตั้ง
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 212 มม.
- สายฉีดน้ำปรับสายน้ำได้ 2 ระดับ แบบดึงเก็บได้
- คอก๊อกน้ำหมุนได้ 360 องศา

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- GB18145-2014
- TIS 2067-2552

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


ก๊อกผสมอ่างล้างจานชนิดหัวฝักบัว K-25981T-4




รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-259081T-4	ก๊อกผสมอ่างล้างจานชนิดหัวฝักบัว รุ่นอะตอม	CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคโธเลอร์ในประเทศของท่าน



กราฟแสดงอัตราการไหล (แบบผสมฟองอากาศ)




กราฟแสดงอัตราการไหล (แบบสเปรย์)

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์