

Features

- Brass construction.
- Leak-free ceramic disc valve with lifetime warranty.
- Durable Kohler finishes resist corrosion and tarnishing.
- Coin aerator allows for easy cleaning and maintenance.
- Adjustable inlet fittings with 15 mm tolerance.
- Includes 5-functions handshower.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB 18145-2014
- TIS 2066-2552
- QB/T 2806-2017


Installation Notes

Install this product according to the installation guide.


Specified Model

Model	Description	Colors/Finishes
K-32877T-4	Atom exposed wall-mount bath shower mixer	CP: Polish chrome

For a full range of color finishes in your market please contact your local Kohler representative.



Flow Curve (Bath outlet)




Flow Curve (Hand shower)

Note: Flow rates are approximate. (1 gallon = 3.758 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลติจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษของโคห์เลอร์ คงทน เงามาม
- ปากก๊อกง่ายต่อการทำความสะอาดและบำรุงรักษา
- อุปกรณ์ติดตั้งกับท่อน้ำเข้าปรับระยะได้ 15 มม.
- พร้อมฝักบัวสายอ่อนปรับสายน้ำได้ 5 ระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- GB 18145-2014
- มก. 2066-2552
- QB/T 2806-2017


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-32877T-4	ก๊อกลดแสงอ่างอาบน้ำและยื่นอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นอะตอม	CP:สีโครมเงา

ตรวจสอบ สี่/วัสดุเคลือบผิวผลิตภัณฑ์ จากตัวแทนจำหน่ายโคโธเลอร์ในประเทศของท่าน



กราฟแสดงอัตราการไหล (กิโลกรัมต่อวินาที)




กราฟแสดงอัตราการไหล (ผักบัวสายอ่อน)

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.758 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์