



Windham™

Elongated toilet bowl

404210

Features

- Elongated bowl only; pairs with Windham toilet tank
- Uses 1.6 gallons of water per flush
- 2" (51 mm) fully glazed trapway

Installation

- 10" (254 mm) rough-in



Codes/Standards

ASME A112.19.2/CSA B45.1
DOE - Energy Policy Act 1992

STERLING® Toilet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White



Windham™
Elongated toilet bowl
404210

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Bowl shape:	Elongated
Flush type:	ProForce Plus
Trap passageway:	2" (51 mm)
Rough-in:	10" (254 mm)

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.