

### Features

- Activation distance is factory-set
- Chloramine and chlorine resistance on all rubber components exposed to waterway
- Engineered for optimal performance with KOHLER® commercial fixtures
- 125-micron filter protects internal components
- High back pressure vacuum breaker
- Locking stop cap provides protection against vandalism
- No external flush volume adjustment ensures water conservation
- 24-hour automatic sentinel flush keeps trapway fresh
- Mechanical override enables flushometer to be used manually even during a power outage
- Powered by a 30 year/875,000 cycle hybrid energy cell, based on 72 uses per day

### Material

- Brass construction with durable Polished Chrome finish

### Technology

- Electronic infrared sensor with Tripoint® technology for accurate activation
- Patented piston technology for superior flush volume accuracy

### Installation

- Intended for urinal installations with 3/4" (19 mm) top spud coupling connection

### Recommended Products/Accessories

- K-23723 Faucet cleaner
- 1421939 Flushometer Arm Extension Kit
- 1509698 Pressure Gauge Kit, 1/8"



ADA

CSA B651

OBC

### Codes/Standards

ASME A112.18.1/CSA B125.1  
ASSE 1037/ASME A112.1037/CSA B125.37  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC  
IAPMO Certification

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.


### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	CP	Polished Chrome
---	----	-----------------

\*10-3/4" (273 mm) minimum with a  
 6" (152 mm) critical level above the fixture



**Technical Information**

All product dimensions are nominal.

- Power source: Hybrid Energy Cell, included
- Drain included: No
- Drain with overflow: No

**Handshower:**

Rated maximum flow: 0 gal/min (0 l/min)

**Pressure/fixture Supply Requirements**

- Fixture pressure max (static): 80 psi (551.6 kPa)
- Fixture pressure min (static): 25 psi (172.4 kPa)
- Min flowing pressure: 25 psi (172.4 kPa)
- Min flow rate: 25 gpm (94.6 lpm)

**Notes**

Install this product according to the installation instructions.  
 ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.