



Underscore® | K-1969-VB

48" x 48" drop-in VibrAcoustic® bath

Features

- Six concealed speakers send sound waves through the water to gently massage the body
- Six original instrumental compositions offer different levels of relaxation
- Syncs with devices enabled with BLUETOOTH® wireless technology including smartphones, MP3 players, tablets, and laptops located up to 33 feet (10 meters) away
- Customize your experience with the high-resolution color touch screen
- Fully-adjustable volume above and below the water
- Functions as a hydrotherapy bath when full of water and a stereo system when empty
- Spacious design accommodates up to two bathers
- Two integral corner seats at different heights
- Extra-deep bathing well for added comfort
- Slotted overflow allows for deep soaking
- Includes 25' of wiring and amplifier



DISCONTINUED



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-29-2026 23:48 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ASME A112.19.7/CSA B45.10
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
UL 1795
CSA C22.2 No. 218.2
cUL Listed
UL Listed

Technical Information

All product dimensions are nominal.

Drain Location:	Center
Drain Hole Diameter:	2-1/2" (64 mm)
Basin Area, Bottom:	39-3/8" x 39-3/8" (1000 mm x 1000 mm)
Basin Area, Top:	44-5/8" x 44-5/8" (1133 mm x 1133 mm)
Water Depth:	27-1/2" (699 mm)
Water Capacity:	171 gal (647.3 L)
Minimum Floor Load:	99 lbs/ft ²
Weight:	115 lbs (52.2 kg)
Cutout:	Drop-in, 47" x 47" (1194 mm x 1194 mm)

Material

- Acrylic

Recommended Products/Accessories

1184460 Kit, Ui Mounting
K-1177 Tiling-in bead, 144" length
K-23726 Drain treatment
K-23732 Tub & shower cleaner

Technology

- VibrAcoustic calms and soothes with sound vibration technology

Connectivity



The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license.

Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Amplifier: 120 V, 15 A, 50/60 Hz

Electrical Component Ratings



Amplifier: 120 V, 1.1 A
Amplifier Channels: 2 at 15 W per channel
2 at 30 W per channel

Warranty

See website for detailed warranty information.


KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty|KOHLER® Hydrotherapy Components Five-Year Limited Warranty






*Recommended User Interface Location


No change in measurements if connected with drain illustrated. (K-8150)



User Interface



Amplifier



Installation

- Drop-in or undermount
- Requires 110 V electrical service

Installation Notes

Install this product according to the installation instructions.

Measure your actual product for rough-in details.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

Control amplifier fits 16" (406 mm) center studs. 25' (7.6 m) cables are included.

IMPORTANT! Due to BLUETOOTH signal overlap, installations of multiple baths within 50 ft (15.2 m) of each other will require special order product. Please contact your dealer, showroom, or sales representative for ordering assistance.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-29-2026 23:48 - US-CA