

### Features

- Modern, simplistic exposed thermostatic valve serves as a hub for shower controls
- Thermostatic valve allows user to set and maintain precise temperature
- Antiscald protection
- Volume control valve provides on/off operation, along with precise control of water volume and intensity
- Includes handshower, 60" (1524 mm) hose, and handshower holder
- Advanced spray engine provides three alternate experiences: wide coverage, intense drenching, and targeted spray
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.38 gpm (9.0 lpm) maximum handshower flow rate at 80 psi (5.5 bar)
- Part of the Aleo S bathroom faucet and showering collection
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

### Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Technology

- Thermostatic technology automatically maintains temperature within +/- 0.4°C (+/- 0.72°F) during water pressure fluctuations

### Installation


- Wall-mount
- G 1/2 inlet connection



### Codes/Standards

Plumbing Standards  
QB/T 2806

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Drain included: No

### Handshower:

Rated maximum flow: 2.38 gal/min (9 l/min)

### Notes

Install this product according to the installation instructions.