

Features


- High-flow thermostatic mixing valve
- Mechanically controlled thermostatic mixing valve maintains outlet temperature throughout shower experience
- Up to 12 gpm (45.4 lpm) flow rate at 45 psi (3.1 bar) with maximum flow of 10 gpm (37.8 lpm) from one outlet
- G 3/4 female inlet connections
- G 1/2 female outlets
- Service stops with integral filters
- Antiscald protection
- Integrated adjustable high-temperature limit stop to control maximum water temperature
- Adjustable comfort setting (preset at approximately 37°C)

Material

- Cast dezincification-resistant brass body provides long term reliability and resistance to aggressive water conditions


Installation

- Requires five-outlet thermostatic valve control panel trim with recessed push buttons (sold separately)
- Fully-serviceable from the front of the valve

**Codes/Standards**

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Pressure/fixture Supply Requirements

Min flowing pressure: 20 psi (137.9 kPa)
Min flow rate: 125 gpm (473.2 lpm)