

**Features**

- High-flow thermostatic mixing valve.
- Mechanically controlled thermostatic mixing valve maintains outlet temperature throughout shower experience.
- Up to 12 gpm (45.4 lpm) flow rate at 45 psi (3.1 bar) with maximum flow of 10 gpm (37.8 lpm) from one outlet.
- G 3/4 female inlet connections.
- G 1/2 female outlets.
- Service stops with integral filters.
- Antiscald protection.
- Integrated adjustable high-temperature limit stop to control maximum water temperature.
- Adjustable comfort setting (preset at approximately 37°C).

**Material**


- Cast dezincification-resistant brass body provides long term reliability and resistance to aggressive water conditions.

**Installation**

- Requires five-outlet thermostatic valve control panel trim with recessed push buttons (sold separately).
- Fully-serviceable from the front of the valve.


**Required Products/Accessories**

K-26349W-9 Five-outlet thermostatic valve control panel

**Codes/Standards**

None Applicable

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Valve body: Cast brass

## Pressure/fixture Supply Requirements

Min flowing pressure: 20 psi (137.9 kPa)

Min flow rate: 125 gpm (473.2 lpm)