

### Features

- Valve Only. Requires KOHLER® glass or metal sensor trim plate and AC or DC power supply (each sold separately) to complete full system solution. Faceplate determines flush volume.
- Designed to be serviceable through faceplate opening
- Adjustable connections for easy installation and servicing
- Fully mechanical manual override
- Lever-handle stop valve for quick and easy water control
- Chloramine and chlorine resistance on all rubber components exposed to waterway
- 125-micron filter protects internal components
- Not for use with PEX piping due to risk of dezincification

### Material

- Durable brass construction

### Installation

- Intended for urinal installations with 3/4" (19 mm) rear spud coupling connection




### Codes/Standards

ASSE 1037/ASME A112.1037/CSA B125.37

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

### Pressure/fixture Supply Requirements

Fixture pressure	80 psi (551.6 kPa)
max (static):	
Fixture pressure min	25 psi (172.4 kPa)
(static):	
Min flow rate:	10 gpm (37.9 lpm)

### Notes

Install this product according to the installation instructions.