

### Features


- Performance showering packages offer increased functionality and simplify the ordering process
- Single lever handle allows for on/off activation, volume, and temperature control
- 6-1/4" (159 mm) diverter spout with G 1/2 connection
- Includes Citrus™ multifunction handshower, handshower holder, and 59" (1500 mm) hose
- Citrus™ multifunction handshower offers five spray experiences: full coverage, wide coverage, dedicated spray, intense drenching, and targeted spray
- Sprayface resists hard water buildup and is easy to clean
- Thumb tab allows for a smooth transition between sprays
- 2.5 gpm (9.5 lpm) maximum handshower flow rate at 73 psi (5.0 bar)
- Handshower holder can be mounted at preferred height to suit your household

### Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Wall-mount
- G 1/2 inlet connection



### Codes/Standards


Plumbing Standards  
TIS 2066-2552

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome



### Technical Information

All product dimensions are nominal.

Drain included: No

### Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

### Notes

Install this product according to the installation guide.