

## Features

- In-line heater provides continuously heated water for consistent comfort
- Front and rear wash modes provide warm water for cleansing
- Adjustable water temperature and water pressure
- Remote control with two programmable user presets
- Continuously heated water with adjustable temperature settings
- Heated seat with adjustable temperature settings
- LED lighting illuminates the bowl to serve as a nightlight
- Warm-air drying system with adjustable air speed and temperature
- Energy-save function
- Quiet-Close™ elongated lid and seat prevents slamming
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning
- Grip-Tight bumpers hold seat firmly in place
- Air blower function allowing selection of air speed and temperature
- Automatic deodorization system for odor control

## Material

- Plastic construction




## Codes/Standards

ASME A112.4.2/CSA B45.16  
CSA C22.2 No. 68  
CSA C22.2 No. 64

## KOHLER® Intelligent Toilet and C3® Cleansing Seat Three-Year Limited Warranty

See website for detailed warranty information.



## Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Bidet toilet seat: 120 V, 15 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Seat shape type: Elongated  
Seat front type: Closed-front  
Seat-mounting holes: 5-1/2" (140 mm)

Electrical component Bidet toilet seat: 120 V, 15 A, 60 Hz rating:

Power cord length: 46" (1168 mm)

## Pressure/fixture Supply Requirements

## Notes

Install this product according to the installation guide.

Locate the receptacle at least 6" (152 mm) above the floor, and within a 32" (813 mm) radius measured 2" (51 mm) from the bowl ledge.

**CAUTION:** Risk of property damage. A single extension cord may be used provided the cord "Type" begins with "SJ", 12 gauge, grounded (12/3), no longer than 25 feet, and plugged into a GFCI outlet. Promptly replace any extension cord that exhibits any sign of damage.