



**C<sup>3</sup>®-125**  
Elongated bidet toilet seat  
**K-4737**

**Features**

- Front and rear wash modes provide warm water for cleansing
- Adjustable water temperature and water pressure
- Heated seat with adjustable temperature settings
- LED lighting illuminates the bowl to serve as a nightlight
- Warm-air drying system with adjustable air speed and temperature
- Side seat controls for convenient access
- Energy-save function
- Quiet-Close™ elongated lid and seat prevents slamming
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning
- Grip-Tight bumpers hold seat firmly in place
- Air blower function allowing selection of air speed and temperature

**Material**

- Plastic construction




**Codes/Standards**

ASME A112.4.2/CSA B45.16  
UL 1431  
CSA C22.2 No. 64  
CSA C22.2 No. 68  
cUL Listed  
UL Listed

**KOHLER® Intelligent Toilet and C3®  
Cleansing Seat Three-Year Limited  
Warranty**

See website for detailed warranty information.



## Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Bidet toilet seat: 120 V, 15 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Seat shape type: Elongated  
Seat front type: Closed-front  
Seat-mounting holes: 5-1/2" (140 mm)

Electrical component rating: Bidet toilet seat: 120 V, 15 A, 60 Hz, 1800 W

Power cord length: 43" (1092 mm)

## Pressure/fixture Supply Requirements

## Notes

Install this product according to the installation guide.

**CAUTION:** Risk of property damage. A single extension cord may be used provided the cord "Type" begins with "SJ", 12 gauge, grounded (12/3), no longer than 25 feet, and plugged into a GFCI outlet. Promptly replace any extension cord that exhibits any sign of damage.

**NOTICE:** Do not plug in the seat until instructed to do so in the installation guide. This will avoid possible product malfunction.

Locate the receptacle at least 6" (152 mm) above the floor, and within a 32" (813 mm) radius measured 2" (51 mm) from the bowl ledge.