



# Invigoration® Series | K-5533

13 kW steam generator

## Features

- Fast-Response® technology produces a luxurious steam shower in 60 seconds
- Power Clean™ technology offers one-touch automatic cleaning and safe maintenance
- 447 cubic feet maximum volume rating for custom showering applications
- Constant Steam feature produces steam at a consistent rate, which greatly minimizes temperature fluctuations
- Invigoration Series steam generators use approximately one gallon of water per 20-minute session, which is significantly less water than a traditional shower experience
- To ensure safety, system automatically shuts down after 20 minutes if not reactivated by user
- Requires K-5557 Invigoration Steam Generator Control Kit or K-5548-K1 Digital Steam Adapter Kit (sold separately)



---

## Codes/Standards

CSA C22.2 No. 64  
cUL Listed

---

## Material

- Generator is constructed of insulated stainless steel, which maintains the temperature while ensuring case is safe to the touch
  - KOHLER finishes resist corrosion and tarnishing
- 

## Recommended Products/Accessories

K-5562 Large drain pan

---

## Required Products/Accessories

- K-5557 Steam generator control kit

or

- K-5548-K1 Digital steam adapter kit
- 

## Required Electrical Service

One dedicated circuit required.

240 V, 80 A, 50/60 Hz


---

## Warranty

*See website for detailed warranty information.*

KOHLER® Steam Generator Three-Year Limited Warranty






Minimum required access panel is 24" (610 mm) L x 15" (381 mm) H.

Allow for a minimum of 12" (305 mm) of space around all sides of the steam generator.

Allow for the drain/spill pan.

KOHLER® drain pan (shown) sold separately.



## Installation Notes

*Install this product according to the installation instructions.*

Steam room volume for this generator is 447 cubic feet (12.7 cubic meters).

For every foot of ceiling height over 8 ft (2.4 m), use the next larger steam unit.

For optimum performance, the steam generator must be installed within 25 ft (7.62 m) of the steam head.

Recommended feed water quality should be: Hardness: 60 ppm (3.4 gpg). Total Alkalinity: 150 ppm (8.8 gpg). To ensure proper operation, the feed water supply should be tested prior to operating the steam generator. If feed water quality is not within the specified limit, contact a reputable water treatment company for treatment options.

Maximum inlet pressure is not to exceed 70 psi (483 kPa).

For supply connection, use 90 degree C copper wire.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada.

7-29-2026 23:57 - US-CA