



Invigoration® Series | K-5547

30 kW steam generator

Features

- Fast-Response® technology produces a luxurious steam shower in 60 seconds
- Power Clean™ technology offers one-touch automatic cleaning and safe maintenance
- 1,000 cubic feet maximum volume rating for custom showering applications
- Constant Steam feature produces steam at a consistent rate, which greatly minimizes temperature fluctuations
- Invigoration Series steam generators use approximately one gallon of water per 20-minute session, which is significantly less water than a traditional shower experience
- To ensure safety, system automatically shuts down after 20 minutes if not reactivated by user
- Requires K-5558 Invigoration Tandem Steam Generator Control Kit or K-5549-K1 DTV+ Tandem Steam Adapter Kit (sold separately)



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-29-2026 23:57 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

CSA C22.2 No. 64
cUL Listed

Warranty

See website for detailed warranty information.

KOHLER® Steam Generator Three-Year Limited Warranty

Technical Information

All product dimensions are nominal.

Recommended Feed Water Quality

Water Hardness: 60 ppm (4 gpg)

Total Water Alkalinity: 150 ppm

Material

- Generator is constructed of insulated stainless steel, which maintains the temperature while ensuring case is safe to the touch
- KOHLER finishes resist corrosion and tarnishing

Recommended Products/Accessories

K-5562 Large drain pan

Required Products/Accessories

- K-5558 Tandem steam generator control kit
- or
- K-5549-K1 Tandem digital steam adapter kit

Required Electrical Service


Two dedicated non-GFCI circuits required.

Steam Generator: 240 V, 90 A, 60 Hz


Electrical Component Ratings

Steam Generator, Steam Generator: 240 V, 60 Hz, 15000 W





Green LED
Diagnostic Light




Minimum required access panel is
24" (610 mm) L x 15" (381 mm) H.

Allow for a minimum of 12" (305 mm) of
space around all sides of the steam generator.

Allow for the drain/spill pan.

KOHLER® drain pan (shown) sold separately.



Installation Notes

Install this product according to the installation instructions.

Steam room volume for this generator is 1000 cubic feet
(28.3 cubic meters).

For optimum performance, the steam generator must be
installed within 25 ft (7.62 m) of the steam head.

Recommended feed water quality should be: Hardness: 60
ppm (3.4 gpg). Total Alkalinity: 150 ppm (8.8 gpg). To ensure
proper operation, the feed water supply should be tested
prior to operating the steam generator. If feed water quality
is not within the specified limit, contact a reputable water
treatment company for treatment options.

Maximum inlet pressure is not to exceed 70 psi (483 kPa).

To ensure proper operation, the feed water supply should be
tested prior to operating the steam generator. If the feed
water quality is not within the specific limit, contact a
reputable water treatment company for treatment options.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-29-2026 23:57 - US-CA