



Iron Works®

66" x 36" drop-in BubbleMassage™ air bath
K-712-GNY

Features

- 43 airjets release thousands of bubbles that surround, support, and massage the body
- Variable-speed blower lets you adjust massage intensity to 18 levels
- Electronic keypad
- Oval basin creates a spacious bathing experience
- Integral lumbar support
- Safeguard® slip-resistant surface provides excellent traction underfoot



Material

- KOHLER® enameled cast iron
- KOHLER® enameled cast iron

Hydrotherapy

- BubbleMassage™

Installation

- Drop-in

Recommended Products/Accessories

- K-1172 Adjustable feet
- K-1491 Bath/Whirlpool Pillow
- K-1601 Bath/whirlpool footstop, removable
- K-7259 Brass toe tap bath drain
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Codes/Standards

- ASME A112.19.1/CSA B45.2
- ASME A112.19.7/CSA B45.10
- ASTM F462
- UL 1795
- CSA C22.2 No. 218.2
- cUL Listed
- UL Listed

KOHLER® Enamelled Cast Iron Bath and Shower Base Lifetime Limited Warranty KOHLER® Hydrotherapy Components Five-Year Limited Warranty

See website for detailed warranty information.

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

2-15-2025 01:19 - US/CA

THE BOLD LOOK
OF **KOHLER**®



Iron Works®
66" x 36" drop-in BubbleMassage™ air bath
K-712-GNY



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Blower: 240 V, 15 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

Drain location: Reversible
Basin area, bottom: 47-1/2" x 25" (1207 mm x 635 mm)
Basin area, top: 55" x 29" (1397 mm x 737 mm)
Weight: 500 lbs (226.8 kg)
Minimum floor load: 65 lbs/ft² (317.4 kg/m²)
Water depth: 12-5/8" (321 mm)
Water capacity: 64 gal (242.3 L)
Template: Drop-in, 88051-7, required, included
Electrical component rating: Blower: 240 V, 5 A, 50/60 Hz
Blower speed: Variable

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

If relocating the blower motor, do not relocate or alter the PVC tee or coiled flexible tubing connected to the blower. Follow the blower relocation instructions exactly. Provide access for servicing the blower.