

#### Features

- Fixture-mount design
- Includes a 30-year hybrid energy cell

#### Material

- Brass

#### Technology

- Electronic infrared sensor with Tripoint® technology for accurate activation
- Slow-closing piston technology

#### Installation

- Intended for urinal installations with 3/4" (19 mm) spud coupling connection

#### Recommended Products/Accessories

K-23723 Faucet cleaner

#### Optional Products/Accessories

GP1118986 Flushometer Extension Kit



ADA

CSA B651

OBC

#### Codes/Standards

ASME A112.18.1/CSA B125.1

CSA B64

CSA B125.3

ASSE 1037/ASME A112.1037/CSA B125.37

ADA

ICC/ANSI A117.1


CSA B651

OBC

#### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

\*10-3/4" (273 mm) minimum with a 6" (152 mm) critical level above the fixture



### Technical Information

All product dimensions are nominal.

Power source: Hybrid Energy Cell, included

### Pressure/fixture Supply Requirements

Fixture pressure max (static): 80 psi (551.6 kPa)

Min flowing pressure: 25 psi (172.4 kPa)

Min flow rate: 10 gpm (37.9 lpm)

### Notes

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.