

## Features

- Fixture-mount design
- Includes a 30-year hybrid energy cell

## Material

- Brass

## Technology

- Electronic infrared sensor with Tripoint<sup>®</sup> technology for accurate activation
- Slow-closing piston technology

## Installation

- Intended for urinal installations with 3/4" (19 mm) spud coupling connection

## Recommended Products/Accessories

K-23723 Faucet cleaner

## Optional Products/Accessories

GP1118986 Flushometer Extension Kit



ADA

CSA B651

OBC

## Codes/Standards

ASME A112.18.1/CSA B125.1

CSA B64

CSA B125.3

ASSE 1037/ASME A112.1037/CSA B125.37

ADA

ICC/ANSI A117.1


CSA B651

OBC

## KOHLER<sup>®</sup> One-Year Limited Warranty

See website for detailed warranty information.

\*10-3/4" (273 mm) minimum with a  
6" (152 mm) critical level above the fixture



## Technical Information

All product dimensions are nominal.

Power source: Hybrid Energy Cell, included

## Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

## Pressure/fixture Supply Requirements

Fixture pressure max (static): 80 psi (551.6 kPa)

Min flowing pressure: 25 psi (172.4 kPa)

Min flow rate: 10 gpm (37.9 lpm)

## Notes

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.