

Features

- Single-stage filtration and absorption system
- Reduces Chlorine Taste & Odor, Chloramine, Particulate Class I, Lead, Asbestos, Cyst, Mercury, Turbidity, and select Pharmaceuticals. See Performance Data Sheet for individual contaminants and reduction performance
- Includes Aquifer single replacement cartridge
- Filter head automatically turns off the water supply when cartridge is removed
- 0.85 gpm maximum flow rate at 60 psi
- Eco-friendly coconut shell-based carbon filter
- Recommended for use with KOHLER® beverage faucets

Material

- High-impact plastic construction

Installation

- Quarter-turn twist cartridge for easy installation and replacement
- Under-sink
- For cold water use only

Recommended Products/Accessories

- K-26369 Beverage faucet
- K-24134 Beverage faucet
- K-24077 Beverage faucet
- K-28291 Beverage faucet
- K-28292 Beverage faucet
- K-26367 Traditional beverage faucet
- K-24074 Beverage faucet
- K-26368 Transitional beverage faucet

Included Components

- K-77687 single replacement filter cartridge




Codes/Standards

CSA B483.1
NSF/ANSI 42
NSF/ANSI 53
NSF/ANSI 401
NSF Protocol P473
IAPMO Certification

KOHLER® Water Filter Systems Five-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 0.85 gal/min (3.2 l/min)

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Notes

Install this product according to the installation guide.

To prevent the risk of property damage, protect from freezing.

For cold water use only.

To ensure the filter continues to reduce contaminants effectively, it is recommended that the filter gets replaced every 6 months.

Application guideline/water supply parameters:

Water Pressure: 40-120 psi (276-827 kPa)

Water Temperature: 33-100°F (0.5-37.8°C)

Capacity: 389 gal (1,472 L)