

## Features

- ContinuousClean system automatically dispenses cleaning solution with every flush
- Works with any white toilet bowl cleaner tablet. Tablets last for more than one year in ContinuousClean system
- Revolution 360® flushing technology generates a forceful swirling motion to keep the bowl clean longer
- 1.28 gpf (4.8 lpf)
- Left-hand Polished Chrome trip lever
- Combines with the K-20485 bowl to create a complete K-90097 Irvine™ ContinuousClean toilet
- Adjustment dial lets you set how much cleaning solution is dispensed with every flush
- Optional: uses two AAA batteries (included) to power the LED system indicator light
- AquaPiston® canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush



## Installation

- Supply line sold separately

## Recommended Products/Accessories

K-20485 Elongated toilet bowl with skirted trapway  
K-23726 Drain treatment

## Codes/Standards






ASME A112.19.2/CSA B45.1  
EPA WaterSense®

## KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	NY	Dune
	95	Ice™ Grey
	7	Black Black™



**Irvine®**  
ContinuousClean XT toilet tank, 1.28 gpf  
**K-90098**

No image available.  
This product is a component and not intended to be a standalone installation.

### Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount  
Waste Outlet: Floor  
Flush type: Revolution 360, AquaPiston

### Fixture Supply Requirements

Min static pressure: 15 psi (103.4 kPa)  
Max static pressure: 80 psi (551.6 kPa)

### Notes

Install this product according to the installation instructions.