

Features

- The bridge and switch module system allows the user to control and operate most electrical devices from the DTV+ interface
- On/off switch module provides control of the electrical device and communication to the DTV+ bridge module
- DTV+ system can control up to three switch modules utilizing the bridge module
- On/off switch modules must be located within 25ft of the bridge module for reliable operation
- Time delay allows users to select a predetermined delay for the lighting module after the system is turned off
- Example applications: Bathroom lighting, bathroom fans, switchable glass, towel warmers

Material


- Premium material construction for durability and reliability

Required Products/Accessories

K-99693-P Digital interface
K-99694 Interface Mounting Bracket
K-99695 System Controller Module

or

K-99693-P Digital interface
K-99694 Interface Mounting Bracket
K-99695-E Eco-system controller module




Codes/Standards

UL 244A
CSA C22.2 No. 14
cUL Listed
UL Listed

KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

Lights: 120 V, 15 A, 60 Hz

Technical Information

All product dimensions are nominal.

Power source: Hardwire - AC, not included

Electrical component rating: Lights: 120 V, 10 A, 60 Hz

Max. Ambient temp: 104°F (40°C)

Max. Relative humidity non-condensing: 95%

Notes

Install this product according to the installation guide.

Recommended that the product be installed by a qualified electrician.

Maximum load is 120 V, 60 Hz, 10 A.

Requires a plastic electrical box 3" (76 mm) x 2" (51 mm) x 2-3/4" (70 mm) or larger, minimum volume of 14 cubic inches.

On/off switch will not work if installed in a metal electrical box.

Do not install to a dimmer switch, a three-way switch, or a switch that controls an electrical outlet.

Install using copper wiring only. Connection to a neutral wire is required.

Building materials may block signal. May need to move the bridge to another location if the switch modules do not pair.

Locate within 25 ft (7.62 m) of the bridge.