

### Sound Enclosure and Subbase Fuel Tank Package



Level 1 Sound Enclosure with Lift Base



Level 2 Sound Enclosure with Subbase Fuel Tank (Shown with optional spill containment)

## **Enclosure and Subbase Fuel Tank Combinations**

Four enclosure configurations are available with the subbase fuel tanks:

- Sound Enclosure Level 1
- Sound Enclosure Level 1, AQMD Ready
- o Sound Enclosure Level 2
- o Sound Enclosure Level 2, AQMD Ready

#### **Available Approvals and Listings**

- ☐ UL 2200 Listing
- UL142 Listing (fuel tanks)
- CSA Approval
- ☐ IBC Seismic Certification
- California OSHPD Approval (KD800-KD1750 models)
- cUL Listing (fuel tanks only)
- ☐ Hurricane Rated Enclosure Available on aluminum Sound Level 2 enclosures, KD800-KD1750 models (Impact rated for Large Missile Level E and Wind load rated per Florida Building Code, tested to TAS201-94, TAS202-94 and TAS203-94 standards)

**NOTE:** Some models may have limited third-party approvals; see your local distributor for details.

# Applicable to the following models: KD800-KD2500 (includes KD1250-A, KD1250-4, KD2500-4)

#### Sound Level 1 Enclosure Standard Features

- Internal silencers with flexible exhaust connectors and exhaust elbows.
- Mounts to lift base and optional subbase fuel tank.
- Aluminum construction with six large, hinged, removable doors for easy maintenance.
- Fade-, scratch-, and corrosion-resistant Kohler<sup>®</sup>
   Power Armor™ automotive-grade textured finish.
- · Lockable, flush-mounted door latches.
- Air inlet louvers to reduce rain and snow entry.
- Sloped roof to reduce the buildup of moisture and debris.
- Acoustic insulation that meets UL 94 HF1 flammability classification.
- Sound level 1 enclosure is designed to 150 mph (241 kph) wind load rating.
- Sound level 1 enclosure uses internal silencers, acoustic insulation and acoustic-lined air inlet hoods.


#### Sound Level 2 Enclosure Standard Features

- Includes all of the sound level 1 enclosure features with the addition of up to 51 mm (2 in.) acoustic insulation material, intake sound baffles, secondary silencers, and vertical air discharge with rain caps.
- Vertical outlet hood with 90 degree angles to redirect air and reduce noise.
- Sound level 2 enclosure is certified to 186 mph (299 kph) wind load rating for KD800-2500 models.

#### **Subbase Fuel Tank Features**

- The fuel tank has a Power Armor Plus<sup>™</sup> textured epoxy-based rubberized coating.
- The above-ground rectangular secondary containment tank mounts directly to the generator set, below the generator set skid (subbase).
- Both the inner and outer tanks have UL-listed emergency relief vents.
- Flexible fuel lines are provided with subbase fuel tank selection.
- The containment tank's construction protects against fuel leaks or ruptures. The inner (primary) tank is sealed inside the outer (secondary) tank. The outer tank contains the fuel if the inner tank leaks or ruptures.
- The above ground secondary containment subbase fuel tank meets UL 142 requirements.
- State tanks with varying capacities are available.
   Florida Dept. of Environmental Protection (FDEP) File
   No. EQ-634 approved.

#### **Aluminum Sound Enclosures**




#### **Level 1 Sound Enclosure Features**

- Heavy-duty formed panels, solid construction.
   Preassembled package offering corrosion resistant, dent resilient structure mounting directly to lift base or fuel tank.
- Polyurethane enamel paint. Superior finish, durability, and appearance.
- The enclosure has a sloped roof to reduce the buildup of moisture and debris.
- Internal exhaust silencers offering maximum component life and operator safety.

**NOTE:** Installing an additional length of exhaust tail pipe may increase backpressure levels. Please refer to the generator set spec sheet for the maximum backpressure value.

- Service access. Multiple personnel doors for easy access to generator set control and servicing of the fuel fill, fuel gauge, oil fill, and battery.
- Interchangeable modular panel construction. Allows complete serviceability or replacement without compromising enclosure design.
- Bolted panels facilitate service, future modification upgrades, or field replacement.
- Cooling/combustion air intake. Fixed air intake louvers.
- Sound-attenuating design using critical silencers. Acoustic insulation UL 94 HF1 listed for flame resistance.
- Horizontal air discharge. Sound level 1 (SL1)
  enclosures use a horizontal design that directs
  exhaust and cooling air out the end of the enclosure.

#### **Aluminum Sound Enclosures**




#### **Level 2 Sound Enclosure Features**

- Heavy-duty formed panels, solid construction.
   Preassembled package offering corrosion resistant, dent resilient structure mounting directly to lift base or fuel tank.
- Polyurethane enamel paint. Superior finish, durability, and appearance.
- The enclosure has a sloped roof to reduce the buildup of moisture and debris.
- Internal exhaust silencers offering maximum component life and operator safety.
- Service access. Multiple personnel doors on both sides for easy access to generator set control and servicing of the fuel fill, fuel gauge, oil fill, and battery.


- Interchangeable modular panel construction. Allows complete serviceability or replacement without compromising enclosure design.
- Bolted panels facilitate service, future modification upgrades, or field replacement.
- Cooling/combustion air intake. Fixed air intake louvers
- Sound-attenuating design using additional secondary silencers and up to 51 mm (2 inches) of added acoustic insulation, UL 94 HF1 listed for flame resistance.
- Vertical air discharge. Sound level 2 (SL2) models use a vertical air discharge design that redirects exhaust and cooling air up and above the enclosure to reduce noise.

#### **Aluminum Sound Enclosure Options**


#### Top view of SL2 enclosure, shown with roof removed for illustration only:



#### Side view of SL2 enclosure, shown with side panels removed for illustration only:



#### **Tier 4 Aluminum Sound Enclosure**



#### Tier 4, Level 2 Sound Enclosure Features

- Available on KD1250-4 and KD2500-4
- Tier 4 options only available with sound level 2 enclosures
- Includes all of the sound level 1 and 2 enclosure features with the addition of DEF tank, SCR, and exhaust collector.
- Remote monitor display
- Locates DEF tanks and lines
- Correctly sizes DEF and diesel tanks
- Service box for control and filter mounting
- Platforms not included

- Diesel fuel state tank is standard
  - o KD1250-4
    - State tank, 5863 L (1549 gal.) or 11205 L (2960 gal.)
    - DEF tank capacity,
      - \* 620 L (164 gal.) with 5863 L (1549 gal.) state tank
      - \* 1241 L (328 gal.) with 11205 L (2960 gal.) state tank
  - o KD2500-4
    - State tank, 14130 L (3733 gal.)
    - DEF tank capacity, 1241 L (328 gal.)

#### **Aluminum Sound Enclosure Options**

#### **Basic Electrical Package (BEP)**

**Distribution Panel/Load Center.** Prewired AC power distribution of all factory-installed features including block heater, two GFCI-protected internal 120-volt service receptacles, internal lighting, and commercial grade wall switches. Single-phase or three-phase load center powered by building source power and protected by a main circuit breaker, rated for 100, 125, or 200 amps as noted, with capacity and circuit positions for future expansion. AC power distribution installed in accordance with NEC and all wiring within EMT thin wall conduit. LED AC lights located within UL-listed fixtures designed for wet locations.

ш	BEP, single-phase, 120/208, 60 Hz or 120/240 VAC, 60 Hz.
	Includes 100 amp electrical panel, two 3-way switches, four
	LED lights, and two GFCI receptacles. *
	BEP, three-phase, 120/208, 60 Hz or 120/240VAC, 60 Hz.

- BEP, three-phase, 120/208, 60 Hz or 120/240VAC, 60 Hz. Includes 125 amp electrical panel, two 3-way switches, four LED lights, and two GFCI receptacles.
- BEP, 200 amp, single-phase, 120/208, 60 Hz or 120/240 VAC, 60 Hz. Includes 200 amp electrical panel, two 3-way switches, four LED lights, and two GFCI receptacles. \*
- □ BEP, 200 amp, three-phase, 120/208, 60 Hz or 120/240VAC, 60 Hz. Includes 200 amp electrical panel, two 3-way switches, four LED lights, and two GFCI receptacles.

#### **DC Light Package**

**DC Light Package (DLP).** Prewired, internal DC light package offering an economical alternative light source within the enclosure, as a complement to the BEP or a source of light when AC power is not available. Battery drain limited with fuse protection and controlled through a 0-60 minute, spring-wound, no-hold timer. Available in LED.

#### **Electrical Accessories**

Wiring Kits. Electrical wiring for accessories. BEP required.

- ☐ Alternator heater wiring (KD1250-2500 only)
- Block heater wiring, single-phase \*
- Block heater wiring, three-phase
- Battery charger wiring
- Wire DEF tank heater †
- Wire power supply (Tier 4 system heaters) §

#### **Emergency Stop Switch**

☐ Generator set emergency stop switch, qty. 1.

#### Note:

Not available with hurricane rated enclosures.

- \* Not available options with Tier 4 generator set enclosures.
- † Only available on enclosed Tier 4 generator set enclosures.
- § Only available on open or enclosed Tier 4 generator sets.

**Stepdown Transformers.** 100 amp BEP required, 60 Hz only. KD1250-2500 only.\*

- ☐ Single-phase, 120/240 V\*
- ☐ Three-phase, 120/208 V \*

**Disconnect Switches.** Disconnect switch for stepdown transformer. 60 Hz only. \*

- □ Single-phase \*
- □ Three-phase \*

#### **Enclosure Heater**

**Heater**, **3.7/5 kW Ceiling Mounted**. Electrical utility heater prewired to load center internal to enclosure. Rated at 17100 Btu. Includes adjustable louvers offering down flow and horizontal air tuning, built-in thermostat with automatic fan delay controls.

- ☐ Heater kit with 1 heater, single/three phase, 208/240 VAC, 60 Hz. BEP required.
- Heater kit with 2 heaters, for KD1250-2500 only, single/three phase, 208/240 VAC, 60 Hz. 200 amp BEP required.

#### **Exhaust Fan**

Exhaust Ventilation Fan. Mounted inside the enclosure.
 BEP required.

Motorized Inlet Louvers. 60 Hz only; BEP required.

- Aluminum construction
- Insulated aluminum construction
- Galvanized construction


Motorized Inlet Louvers. 60 Hz only; BEP required.

- Aluminum construction
- Insulated aluminum construction
- Galvanized construction

#### **Gravity Air Outlet**

Aluminum construction

#### **Subbase Fuel Tank**



#### Subbase Fuel Tank Standard Features

- Extended operation. State tanks with various capacities for multiple hour requirements.
- UL listed. Secondary containment generator set base tank meeting UL 142 requirements.
- NFPA compliant. Designed to comply with the installation standards of NFPA 30 and NFPA 37.
- Integral external lift lugs. Enables crane with spreaderbar lifting of the complete package (empty tank, mounted generator set, and enclosure) to ensure safety.
- Emergency pressure relief vents. Vents ensure adequate venting of inner and outer tank under extreme pressure and/or emergency conditions.
- Normal vent with cap. Vent is raised above lockable fuel fill.
- Fuel level gauge with sender.
- Mechanical fuel level gauge.
- Leak detection switch. Annunciates a contained primary tank fuel leak condition at generator set control.
- Electrical stub-up area open to bottom.
- Additional 2 in. NPT fittings for optional accessories.

#### **Subbase Fuel Tank Options**

#### **Bottom Clearance**

☐ I-beams, provide 102 mm (4 in.) of ground clearance (not available with OSHPD or IBC seismic certification)

#### **Emergency Vent Options**

- □ 127 mm (5 in.), IBC
- ☐ 152.4 mm (6 in.), IBC KD800-1000 12 hr. tank only

#### **Fuel in Basin Options**

- ☐ Fuel in basin switch, Florida Dept. of Environmental Protection (FDEP) File No. EQ-682 approved
- □ 100% engine fluid containment

#### **Fuel Supply Options**

- ☐ Fire safety valve (installed on fuel supply line)
- Ball valve (installed on fuel supply line)

#### **Fuel Fill Options**

- ☐ Fill pipe extension to within 152 mm (6 in.) of bottom of fuel tank
- ☐ 18.9 L (5 gallon) spill containment
- 18.9 L (5 gallon) spill containment with 95% shutoff
- □ 18.9 L (5 gallon) spill containment fill to within 152 mm (6 in.) of bottom of fuel tank
- ☐ 18.9 L (5 gallon) spill containment, OSHPD/IBC
- 18.9 L (5 gallon) spill containment with 95% shutoff, OSHPD/IBC
- 28.4 L (7.5 gallon) spill containment, Florida Dept. of Environmental Protection (FDEP) File No. EQ-345 approved
- 28.4 L (7.5 gallon) spill containment with 95% shutoff, Florida Dept. of Environmental Protection (FDEP) File No. EQ-345/EQ-257 approved

#### **High Fuel Level Switch**

- ☐ High fuel level switch, 24V
- ☐ High fuel level switch, 24V, Florida Dept. of Environmental Protection (FDEP) File No. EQ-682 approved
- ☐ Fuel tank panel, 3 alarm, 24 V
- ☐ Fuel tank panel, 3 alarm, 24 V, Florida Dept. of Environmental Protection (FDEP) File No. EQ-682 approved

#### **Normal Vent Options**

- □ 3.7 m (12 ft.) above grade (without spill containment)
- 3.7 m (12 ft.) above grade (with spill containment)

#### Freestanding Stairs

- Stairs only, single door access
- ☐ Stairs with platform, single door access
- ☐ Stairs with catwalk, 2 door access, door length only
- Stairs with catwalk, 2 door access, full length of enclosure

#### **Tank Marking Options**

- Decal, Combustible Liquids Keep Fire Away (qty. 2)
- Decal, NFPA 704 identification (qty. 2)
- ☐ Decal, tank number and safe fuel fill height (qty. 2)

#### **Enclosure and Subbase Fuel Tank Specifications**

Fuel Tank	Est. Fuel Supply Hours at 60 Hz with Full	Max Dimensions mm (in )			Max Weight +	Fuel Tank Height.	Sound Pressure Level at 60 Hz with Full
Capacity, L (gal.)	Load (nominal)	Length	Width §	Height	Max. Weight, † kg (lb.)	Height, mm (in.)	Load, dB(A) ‡
KD800 SL1 Sour	nd Enclosure	e with Internal S	Silencer and S	State Code Subl	pase Fuel Tank *		
Lifting Base	0	6582 (259)		3350 (132)	10184 (22452)	_	
3475 (918)	12			3706 (146)	13772 (30362)	356 (14.0)	
6621 (1749)	24	7309 (288)	2616 (103)	3934 (155)	14252 (31421)	584 (23.0)	90
10573 (2793)	48			4264 (168)	14831 (32698)	914 (36.0)	
15740 (4158)	72	9144 (360)		4366 (172)	16242 (35808)	1016 (40.0)	
KD800 SL2 Sour	nd Enclosure	e with Internal S	Silencer and S	State Code Subl	pase Fuel Tank *		
Lifting Base	0	7707 (303)		3350 (132)	10587 (23340)	_	
3475 (918)	12		1	3706 (146)	14175 (31250)	356 (14.0)	1
6621 (1749)	24	8434 (332)	2616 (103)	3934 (155)	14655 (32309)	584 (23.0)	75
10573 (2793)	48			4290 (169)	15234 (33586)	915 (36.0)	]
15740 (4158)	72	9144 (360)		4366 (172)	16645 (36696)	1016 (40.0)	
KD900 SL1 Sour	nd Enclosure	e with Internal :	Silencer and S	State Code Subl	pase Fuel Tank *		
Lifting Base	0	6582 (259)		3350 (132)	10497 (23343)	_	
3475 (918)	12		1	3706 (146)	14085 (31253)	356 (14.0)	
6621 (1749)	24	7309 (288)	2616 (103)	3934 (155)	14565 (32312)	584 (23.0)	91
12969 (3426)	48	8400 (331)	1	4293 (169)	16348 (36243)	940 (37.0)	
19381 (5120)	72	11050 (435)	1	4369 (172)	17527 (38840)	1016 (40.0)	
KD900 SL2 Sour	nd Enclosure	e with Internal S	Silencer and S	State Code Subl	pase Fuel Tank *		
Lifting Base	0	7707 (303)		3350 (132)	10900 (24231)	_	
3475 (918)	12	` ,	1	3706 (146)	14488 (32141)	356 (14.0)	
6621 (1749)	24	8434 (332)	2616 (103)	3934 (155)	14968 (33200)	584 (23.0)	75
12969 (3426)	48	, ,	, ,	4290 (169)	16751 (37131)	940 (37.0)	
19381 (5120)	72	11050 (435)	1	4366 (172)	17930 (39728)	1016 (40.0)	
KD1000 SL1 Sou	ınd Enclosu	re with Internal	Silencer and	State Code Sul	base Fuel Tank *		
Lifting Base	0	6582 (259)		3350 (132)	10810 (23833)	_	
3475 (918)	12	, ,	1	3706 (146)	14398 (31743)	356 (14.0)	
6621 (1749)	24	7309 (288)	2616 (103)	3934 (155)	14878 (32802)	584 (23.0)	92
12969 (3426)	48	8400 (331)	1 ` ´	4290 (169)	16661 (36733)	940 (37.0)	
19381 (5120)	72	11050 (435)	1	4366 (172)	17840 (39330)	1016 (40.0)	
KD1000 SI 2 Sou	ınd Enclosu	re with Internal	Silencer and	State Code Sul	bbase Fuel Tank *		•
Lifting Base	0	7707 (303)	Jiionijoi unu	3353 (132)	11213 (24721)		
3475 (918)	12	(000)	1	3706 (146)	14801 (32631)	356 (14.0)	
6621 (1749)	24	8434 (332)	2616 (103)	3934 (155)	15281 (33690)	584 (23.0)	76
12969 (3426)	48	0.0.(002)		4290 (169)	17064 (37621)	940 (37.0)	, ,
			4	( /	()	()	1

<sup>\*</sup> Data in table is for reference only. Height includes enclosure, lift base, and tank (if equipped). Refer to your authorized Kohler distributor for enclosure and subbase fuel tank specification details.

<sup>†</sup> Max. weight includes the generator set (wet) with the largest alternator option, enclosure, silencers, lift base, and tank (no fuel).

<sup>‡</sup> Log average sound pressure level of 8 measured positions around the perimeter of the unit at a distance of 7 m (23 ft). Refer to TIB-114 for details. Enclosed generator set sound data for some models was not available at time of print.

<sup>§</sup> An additional 940 mm (37 inches) of clearance on each side for opening and closing the access doors is recommended. **Note:** 

#### **Enclosure and Subbase Fuel Tank Specifications, continued**

	Est. Fuel				rank opecinications,		
Fuel Tank	Supply Hours at 60 Hz with Full	Max. Dimensions, mm (in.)				Fuel Tank	Sound Pressure Level at 60 Hz with Full
Capacity, L (gal.)	Load (nominal)	Length	Width §	Height	Max. Weight, † kg (lb.)	Height, mm (in.)	Load, dB(A) ‡
KD1250-4 SL2 Sc		ure with State	Code Subbas				T
5863 (1549)	17	11147 (439)	3033 (119)	4640 (183)	22507 (49619)	381 (15.0)	75
11204 (2960)	33	(100)	0000 (110)	4894 (193)	23731 (52318)	635 (25.0)	. 0
KD1250-A/1350 S	SL1 Sound E	Enclosure with	Internal Silen	cers and State	Code Subbase Fuel Tank *		
Lifting Base	0	8831 (348)		3579 (141)	17116 (37748)	_	
5863 (1549)	18/17			3960 (156)	22326 (49234)	381 (15.0)	
9860 (2605)	30/29	9594 (378)	2022 (440)	4138 (163)	22808 (50296)	559 (22.0)	93
11204 (2960)	34/32		3033 (119)	4214 (166)	22973 (50661)	635 (25.0)	93
19214 (5076)	58/56	44442 (420)		4468 (176)	25277 (55741)	889 (35.0)	
21985 (5808)	67/64	11113 (438)		4570 (180)	25684 (56637)	991 (39.0)	
KD1250-A/1350 S	SL2 Sound E	nclosure with	Internal Silen	cer and State (	Code Subbase Fuel Tank *		
Lifting Base	0	10420 (410)		3579 (141)	18031 (39764)	_	
5863 (1549)	18/17	,		3960 (156)	23241 (51250)	381 (15.0)	
9860 (2605)	30/29			4138 (163)	23723 (52312)	559 (22.0)	76
11204 (2960)	34/32	11147 (439)	3033 (119)	4214 (166)	23888 (52677)	635 (25.0)	1
19214 (5076)	58/56			4468 (176)	26192 (57757)	889 (35.0)	
21985 (5808)	67/64			4570 (180)	26599 (58653)	991 (39.0)	
KD1E00 SI 1 Sau	and Englosus	ro with Internal	Silonooro on	d State Code S	ubbase Fuel Tank *		I
Lifting Base	0	8831 (348)	Silencers and	3579 (141)	17116 (37748)	T _	
5863 (1549)	18/15	3331 (3.3)		3960 (156)	22326 (49234)	381 (15.0)	
9860 (2605)	30/25	9594 (378)		4138 (163)	22808 (50296)	559 (22.0)	
11204 (2960)	34/28	(0.0)	3033 (119)	4214 (166)	22973 (50661)	635 (25.0)	93
19214 (5076)	58/48			4468 (176)	25277 (55741)	889 (35.0)	
21985 (5808)	66/55	11113 (438)		4570 (180)	25684 (56637)	991 (39.0)	
. ,			011	` '	, ,	101 (0010)	
Lifting Base	0	10420 (410)	Silencer and	3579 (141)	18031 (39764)		
	18/15	10420 (410)		` '	,	291 (15.0)	
5863 (1549)				3960 (156)	23241 (51250)	381 (15.0)	
9860 (2605) 11204 (2960)	30/25 34/28	11147 (439)	3033 (119)	4138 (163) 4214 (166)	23723 (52312) 23888 (52677)	559 (22.0) 635 (25.0)	79
		11147 (438)					
19214 (5076)	58/48			4468 (176)	26192 (57757)	889 (35.0)	
21985 (5808)	66/55			4570 (180)	26599 (58653)	991 (39.0)	
			Silencers and		ubbase Fuel Tank *	Г	Т
Lifting Base	0	8831 (348)		3579 (141)	17343 (38248)		
5863 (1549)	14			3960 (156)	22553 (49734)	381 (15.0)	
9860 (2605)	23	9594 (378)	3033 (119)	4138 (163)	23035 (50796)	559 (22.0)	94
11204 (2960)	26		3555 (110)	4214 (166)	23200 (51161)	635 (25.0)	
19214 (5076)	45	11113 (438)		4468 (176)	25504 (56241)	889 (35.0)	
21985 (5808)	52	(.00)		4570 (180)	25911 (57137)	991 (39.0)	

- \* Data in table is for reference only. Height includes enclosure, lift base, and tank (if equipped). Refer to your authorized Kohler distributor for enclosure and subbase fuel tank specification details.
- Tier 4 generator enclosure height includes the fuel tank and enclosure up to the exhaust flange. The height does not include the SCR, or the SCR inlet and outlet pipes.
- \*\* Tier 4 generator enclosure weight includes the DEF tank but does not include the SCR or the SCR inlet and outlet pipes.
- † Max. weight includes the generator set (wet) with the largest alternator option, enclosure, silencers, lift base, and tank (no fuel).
- ± Log average sound pressure level of 8 measured positions around the perimeter of the unit at a distance of 7 m (23 ft). Refer to TIB-114 for details. Enclosed generator set sound data for some models was not available at time of print.
- § An additional 940 mm (37 inches) of clearance on each side for opening and closing the access doors is recommended.

#### Note:

_	raint opcomoations,	Jonana	
Est. Fuel Supply Hours at			Sound Pressure

٦

Enclosure and Subbase Fuel Tank Specifications, continued

Fuel Tank	Supply Hours at 60 Hz with Full	Max. Di	imensions, mı	m (in.)		Fuel Tank	Sound Pressure Level at 60 Hz with Full
Capacity, L (gal.)	Load (nominal)	Length	Width §	Height	Max. Weight, † kg (lb.)	Height, mm (in.)	Load, dB(A) ‡

#### KD1600 SL2 Sound Enclosure with Internal Silencer and State Code Subbase Fuel Tank \*

Lifting Base	0	10420 (410)		3579 (141)	18258 (40264)	_	
5863 (1549)	14			3960 (156)	23468 (51750)	381 (15.0)	
9860 (2605)	23		2022 (440)	4138 (163)	23950 (52812)	559 (22.0)	79
11204 (2960)	26	11147 (439)	3033 (119)	4214 (166)	24115 (53177)	635 (25.0)	79
19214 (5076)	45			4468 (176)	26419 (58257)	889 (35.0)	
21985 (5808)	52			4570 (180)	26826 (59153)	991 (39.0)	

#### KD1750 SL1 Sound Enclosure with Internal Silencers and State Code Subbase Fuel Tank \*

Lifting Base	0	8831 (348)		3579 (141)	17343 (38248)	_	
5863 (1549)	13			3960 (156)	22553 (49734)	381 (15.0)	
9860 (2605)	21	9594 (378)	3033 (119)	4138 (163)	23035 (50796)	559 (22.0)	95
11204 (2960)	24		3033 (119)	4214 (166)	23200 (51161)	635 (25.0)	95
19214 (5076)	42	11113 (438)		4468 (176)	25504 (56241)	889 (35.0)	
21985 (5808)	48	11113 (436)		4570 (180)	25911 (57137)	991 (39.0)	

#### KD1750 SL2 Sound Enclosure with Internal Silencer and State Code Subbase Fuel Tank \*

Lifting Base	0	10420 (410)		3579 (141)	18258 (40264)	_	
5863 (1549)	13			3960 (156)	23468 (51750)	381 (15.0)	
9860 (2605)	21		3033 (119)	4138 (163)	23950 (52812)	559 (22.0)	79
11204 (2960)	24	11147 (439)	3033 (119)	4214 (166)	24115 (53177)	635 (25.0)	79
19214 (5076)	42			4468 (176)	26419 (58257)	889 (35.0)	
21985 (5808)	48			4570 (180)	26826 (59153)	991 (39.0)	

KD2000/2250/2500 (KD62V12 Engine) SL1 Sound Enclosure with Internal Silencers and State Code Subbase Fuel Tank \*

INDEGOGIEE CON ECO	O (INDOLVIA	. Engine/ oer o	ouna Endios	are with miter	iai olicilocio alla otate ocae oai	base i aci i alii	<u> </u>
Lifting Base	0	10774 (424)	3488 (137)	4141 (163)	33073 (72909)	_	90
8577 (2266)	15/14/13			4522 (178)	40485 (89252)	381 (15)	
14130 (3733)	25/22/22	11465 (451)	3400 (137)	4700 (185)	41216 (90861)	559 (22)	90
16451 (4346)	29/26/25			4776 (188)	41497 (91483)	635 (25)	

KD2000/2250/2500 (KD62V12 Engine) SL2 Sound Enclosure with Internal Silencer and State Code Subbase Fuel Tank \*

Lifting Base	0	12766 (503)		4141 (163)	35121 (77426)		
8577 (2266)	15/14/13		2400 (427)	4522 (178)	42533 (93766)	381 (15)	70
14130 (3733)	25/22/22	13491 (531)	3488 (137)	4700 (185)	43264 (95378)	559 (22)	78
16451 (4346)	29/26/25			4776 (188)	43545 (95997)	635 (25)	

KD2000/2250/2500 (KD62V12A Engine) SL1 Sound Enclosure with Internal Silencers and State Code Subbase Fuel Tank \*

Lifting Base	0	10774 (424)		4141 (163)	33073 (72909)	_	
8577 (2266)	16/14/13		3488 (137)	4522 (178)	40485 (89252)	381 (15)	90
14130 (3733)	26/23/22	11465 (451)	3400 (137)	4700 (185)	41216 (90861)	559 (22)	90
16451 (4346)	31/27/25			4776 (188)	41497 (91483)	635 (25)	

- Data in table is for reference only. Height includes enclosure, lift base, and tank (if equipped). Refer to your authorized Kohler distributor for enclosure and sub-base fuel tank specification details.
- ◆ Tier 4 generator enclosure height includes lift base, tank, and enclosure up to exhaust flange. The height does not include the exhaust collector, SCR, or the SCR inlet and outlet pipes.
- Tier 4 generator enclosure weight includes the DEF tank but does not include the SCR or the SCR inlet and outlet pipes.
- Max. weight includes the generator set (wet) with the largest alternator option, enclosure, silencers, lift base, and tank (no fuel).
- ‡ Log average sound pressure level of 8 measured positions around the perimeter of the unit at a distance of 7 m (23 ft). Refer to TIB-114 for details. Enclosed generator set sound data for some models was not available at time of print.
- An additional 940 mm (37 inches) of clearance on each side for opening and closing the access doors is recommended.

#### **Enclosure and Subbase Fuel Tank Specifications, continued**

Fuel Tank	Est. Fuel Supply Hours at 60 Hz with Full	Max. Dimensions, mm (in.)				Fuel Tank	Sound Pressure Level at 60 Hz with Full
Capacity,	Load				Max. Weight, †	Height,	Load,
L (gal.)	(nominal)	Length	Width §	Height	kg (lb.)	mm (in.)	dB(A) ‡

KD2000/2250/2500 (KD62V12A Engine) SL2 Sound Enclosure with Internal Silencer and State Code Subbase Fuel Tank \*

Lifting Base	0	12766 (503) 13491 (531)	3488 (137)	4141 (163)	35121 (77426)		78
8577 (2266)	16/14/13			4522 (178)	42533 (93766)	381 (15)	
14130 (3733)	26/23/22			4700 (185)	43264 (95378)	559 (22)	
16451 (4346)	31/27/25			4776 (188)	43545 (95997)	635 (25)	

14130 (3733)     21     13491 (531)     3488 (137)     4907 (193)     43583 (96084)     559 (22)	78
--	----

- \* Data in table is for reference only. Height includes enclosure, lift base, and tank (if equipped). Refer to your authorized Kohler distributor for enclosure and sub-base fuel tank specification details.
- Tier 4 generator enclosure height includes lift base, tank, and enclosure up to exhaust flange. The height does not include the exhaust collector, SCR, or the SCR inlet and outlet pipes.
- I Tier 4 generator enclosure weight includes the DEF tank but does not include the SCR or the SCR inlet and outlet pipes.
- † Max. weight includes the generator set (wet) with the largest alternator option, enclosure, silencers, lift base, and tank (no fuel).
- ‡ Log average sound pressure level of 8 measured positions around the perimeter of the unit at a distance of 7 m (23 ft). Refer to TIB-114 for details. Enclosed generator set sound data for some models was not available at time of print.
- § An additional 940 mm (37 inches) of clearance on each side for opening and closing the access doors is recommended.

#### Note:



KOHLER CO., Kohler, Wisconsin 53044 USA Phone 920-457-4441, Fax 920-459-1646 For the nearest sales and service outlet in the US and Canada, phone 1-800-544-2444 KOHLERPower.com

DISTRIBUTED BY	•
----------------	---

Availability is subject to change without notice. Kohler Co. reserves the right to change the design or specifications without notice and without any obligation or liability whatsoever. Contact your local Kohler® generator set distributor for availability.

© 2016 Kohler Co. All rights reserved.