

# KALLISTA®

## Script® Decorative by KALLISTA

Sink faucet, low spout, Frost enamel lever handles  
P25054-FRW

### Features

- Handcrafted fired enamel handle insert with Wave pattern
- High-quality solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- Spout reach is 5-1/2" (140 mm)
- Aerated flow
- Includes drain and lift rod
- 1.2 gpm (4.5 lpm) maximum flow rate

### Recommended Products/Accessories

P74241-WO Under-mount Sink, Soft Oval with Overflow, Glazed

P25006-CR Script Sink Faucet, Low Spout, Cross Handles

P25041-00 Towel Bar, 24"

P25046-00 Hook



**ADA**

**CSA B651**

**OBC**

### Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

CSA B651

OBC

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BAF	Brushed French Gold
	BN	Brushed Nickel
	BV	Brushed Bronze
	SN	Polished Nickel

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

2-15-2025 21:53 - US/CA

# KALLISTA

Script® Decorative by KALLISTA  
Sink faucet, low spout, Frost enamel lever handles  
P25054-FRW



## Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes  
Drain with overflow: Yes

## Spout:

Spout reach: 5-3/16" (131 mm)

## Pressure/fixture Supply Requirements

Min flow rate: 1.2 gpm (4.5 lpm)

## Notes

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

2-15-2025 21:53 - US/CA