

# KALLISTA®

## Script® Decorative by KALLISTA Sink faucet, arch spout, White Porcelain knob handles P25057-CMC

### Features

- Handcrafted porcelain handles
- High-quality solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- Spout reach is 6-9/16" (167 mm)
- Includes soft-touch drain
- 1.2 gpm (4.5 lpm) maximum flow rate
- Aerated flow

### Recommended Products/Accessories

P74241-WO Under-mount Sink, Soft Oval with Overflow, Glazed  
P25054-SPR Sink faucet, low spout, Spring Rain lever handles  
P25043-00 Towel Bar, 18"  
P25046-00 Hook

IMAGE COMING SOON



### Codes/Standards







ASME A112.18.1/CSA B125.1  
NSF/ANSI/CAN 61  
NSF/ANSI/CAN 372  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color   | Code | Description         |
|---|------|---------------------|
|  | CP   | Polished Chrome     |
|  | BCH  | Blush Bronze        |
|  | BAF  | Brushed French Gold |
|  | BN   | Brushed Nickel      |
|  | BV   | Brushed Bronze      |
|  | SN   | Polished Nickel     |

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

2-15-2025 21:53 - US

# KALLISTA

Script® Decorative by KALLISTA  
Sink faucet, arch spout, White Porcelain knob  
handles  
P25057-CMC



## Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 6-3/16" (157 mm)

## Notes

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.