

### Features

- Trim plate includes temperature control knob with integrated adjustable high-temperature limit stop and shower outlet on/off buttons
- When pressed once, shower outlet turns on and button pops out, becoming a knob for water flow adjustment
- When pressed back in, water turns off and outlet button aligns with control plate surface; flow setting remains intact
- High-temperature limit setting for added safety
- Low-profile design with easy-to-clean water-resistant casing
- Requires two-port thermostatic valve with integral volume control (sold separately)
- Handles up to 8 gpm (30.3 lpm) flow capacity (rate may vary by installation)



### Installation

- Mounts on finished wall surface

### Required Products/Accessories

P34723-00 Mechanical showering two-port thermostatic valve with integrated volume control

### Codes/Standards










ASME A112.18.1/CSA B125.1

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.




### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	BN	Brushed Nickel
	BAF	Brushed French Gold
	PB	Polished Brass
	SN	Polished Nickel
	BV	Brushed Bronze
	AF	French Gold
	2MB	Brushed Moderne Brass

# KALLISTA

Foundations by KALLISTA  
Mechanical showering two-outlet thermostatic  
control panel  
P34719-00



## Technical Information

All product dimensions are nominal.

## Notes

Install this product according to the installation instructions.