

# rehlko



Kohler Engines  
is now Rehlko

## Command PRO<sup>®</sup>

Gasoline Engines

**24.2 – 28.3 kW | 32.5 – 38 hp**

The Command PRO<sup>®</sup> EFI engine saves gas and reduces downtime, giving you the power to cut costs and cover more ground every day.



# The *muscle* you need For commercial applications

Whatever the job or power range, the Command PRO® 999 cc engine—models from 32.5 to 38 hp—takes the gas engine to powerful heights of horsepower, torque and reliability. Redesigned to feature the latest engine cooling technology to improve durability.



PROVEN DURABILITY  
AND RELIABILITY



EXCEPTIONAL  
PERFORMANCE



EASY TO MAINTAIN

\*Class defined as EPA Class I gasoline engines 225 cc or below.



# Command PRO®

## Standard features

Hydraulic valve lifters for quiet operation, no adjustments

High-efficiency fan and screen for superior cooling and longer engine life

15-Amp charging, regulated

Front-mount controls for easy operation and OEM installation

Easily accessible service points

Full-pressure lubricant with filter and Oil Sentry™ automatic low-oil/shutdown system

Large dual drains for faster oil changes

Hardened crank journals for long-life 12-volt solenoid shift starter

3-Year limited warranty

Electronic ignition with high-performance spark plugs

Solenoid fuel shutdown to limit afterbang

## Popular factory options

Canister mufflers with right, left and center outlets

Filter minder for heavy-duty air cleaner

Guard for rotating grass screen

Engine-mounted controls (CH models)

Remote oil filter exhaust deflector

Spark arrestor

20- and 25-Amp charging systems

11/8- and 17/16-inch crankshaft diameters

Front drive shaft


Customer mounting pilot (CH models)

EMC- and RFI-compliant




# Command PRO®

## 27–30 HP Horizontal-Shaft Engines\*




Front view




PTO view

### Data

Dimensions (mm)



Starter side view




Oil filter side view

MODEL		CH940	CH980	CH1000
<b>POWER @ 3600 rpm</b>	Max.hp (kW)	32.5 (24.2)	35 (26.1)	37 (27.5)
<b>DISPLACEMENT</b>	cu in (cc)		61 (999)	
<b>BORE</b>	in (mm)		3.5 (90)	
<b>STROKE</b>	in (mm)		3.1 (78.5)	
<b>PEAK TORQUE @ rpm</b>	ft-lb (Nm)	53.5 (71.8) @ 2600	54.3 (73.6) @ 3400	57.4 (77.8) @ 3200
<b>COMPRESSION RATIO</b>			8.8:1	
<b>DRY WEIGHT</b>	lb (kg)		131 (60)	
<b>OIL CAPACITY</b>	U.S. qt (L)		2.0 (1.9)	
<b>LUBRICATION</b>		FULL-PRESSURE LUBRICATION WITH FULL-FLOW FILTER		
<b>DIMENSIONS L x W x H</b>	in (mm)	LOW-PROFILE AIR CLEANER 15.8 X 19.1 X 23.6 (402 X 484 X 600) HEAVY-DUTY AIR CLEANER 17.1 X 19.1 X 27.5 (435 X 484 X 699)		


\* With Heavy-Duty Air Cleaner

### Maximum power



— CH940  
— CH980  
— CH1000

### Maximum torque



— CH940  
— CH980  
— CH1000




# Command PRO® EFI


35–38 HP Horizontal-Shaft Engines\*

## Data


Dimensions (mm)




Front view



PTO view



Starter side view




Oil filter side view

MODEL		ECH940	ECH980
<b>POWER @ 3600 rpm</b>	Max.hp (kW)	35 (26.1)	38 (28.3)
<b>SHAFT</b>		HORIZONTAL	
<b>DISPLACEMENT</b>	cu in (cc)	61 (999)	
<b>BORE</b>	in (mm)	3.5 (90)	
<b>STROKE</b>	in (mm)	3.1 (78.5)	
<b>PEAK TORQUE @ rpm</b>	ft-lb (Nm)	56.0 (75.9) @ 3000	56.0 (75.9) @ 3000
<b>COMPRESSION RATIO</b>		8.8:1	
<b>DRY WEIGHT</b>	lb (kg)	132 (60)	
<b>OIL CAPACITY</b>	U.S. qt (L)	2.0 (1.9)	
<b>LUBRICATION</b>		FULL-PRESSURE WITH FULL-FLOW FILTER	
<b>DIMENSIONS L x W x H</b>	in (mm)	LOW-PROFILE AIR CLEANER 15.8 X 19.1 X 23.6 (402 X 484 X 600) HEAVY-DUTY AIR CLEANER 17.1 X 19.1 X 27.5 (435 X 484 X 699)	


\* With Low-Profile Air Cleaner

### Maximum power



— ECH940  
— ECH980

### Maximum torque





— ECH940  
— ECH980

# Command PRO® EFI

35–38 HP Vertical-Shaft Engines\*


## Data

Dimensions (mm)




MODEL		ECV940	ECV980
<b>POWER @ 3600 rpm</b>	Max.hp (kW)	35 (26.1)	38 (28.3)
<b>SHAFT</b>		VERTICAL	
<b>DISPLACEMENT</b>	cu in (cc)	61 (999)	
<b>BORE</b>	in (mm)	3.5 (90)	
<b>STROKE</b>	in (mm)	3.1 (78.5)	
<b>PEAK TORQUE @ rpm</b>	ft-lb (Nm)	53.0 (71.8) @ 3200	56.9 (72.2) @ 3400
<b>COMPRESSION RATIO</b>		8.8:1	
<b>DRY WEIGHT</b>	lb (kg)	134 (61)	
<b>OIL CAPACITY</b>	U.S. qt (L)	2.0 (1.9)	
<b>LUBRICATION</b>		FULL-PRESSURE WITH FULL-FLOW FILTER	
<b>DIMENSIONS L x W x H</b>	in (mm)	22.1 X 19.1 X 26.8 (560 X 485 X 681)	

### Maximum power



### Maximum torque



\* With Heavy-Duty Air Cleaner



For more information, contact your Rehlko source of supply.

Discovery Energy, LLC reserves the right to make modifications without prior notice.

[engines.rehlko.com](https://engines.rehlko.com)

