
rehlko



Kohler Engines is now Rehlko

KSD Series

Diesel Engines

18.4 kW | 24.7 hp

Simple, advanced, versatile. Experience the next level of engine technology, compatible with all kinds of non-road machines, compliant with all global exhaust emissions norms.







ELECTRONIC FUEL INJECTION

SAVES TIME AND INCREASES PRODUCTIVITY

DURABLE COMPONENTS



SIMPLE, ADVANCED, VERSATILE

EASY-TO-INTEGRATE SOLUTIONS

COMPATIBLE WITH ALL KINDS OF MACHINES



COMPLIANT WITH ALL EMISSIONS STANDARDS WORLDWIDE

Innovations and benefits

EMISSIONS STANDARDS

The wide variety of emission standards has introduced a new level of complexity to the engines business.

The KOHLER KSD is a new base engine below 19 kW that complies with all global emissions standards and fuels.

ELECTRONIC CONTROL

The versatility of KOHLER KSD engines goes beyond performance, with the ability to easily fit into existing machine platforms. KOHLER KSD engines are electronically managed, while being as simple to use as mechanical engines. The fuel system allows precise fuel metering and excellent load response, resulting in increased productivity. Moreover, KSD engines offer switchability for gensets.

COMBUSTION SYSTEM

The innovative technology brought on by the KOHLER KSD is its architecture: it features a state-of-the-art indirect injection system but has the electronic management typical of direct injection engines.

- The engine performance is maximized in every operating condition and environment
- · Outstanding engine response
- The remarkable low-end torque values allow the operator to run their piece of equipment at lower rpm to save fuel
- The electronic injection system results in no visible black smoke
- · Noise and vibrations are minimized

EASE OF INSTALLATION

KOHLER KSD engines do not require any kind of machine re-designing from OEMs. As a result, KOHLER KSD engines offer a drop-in solution for existing applications.

SERVICE & TOTAL COST OF OWNERSHIP

KOHLER KSD engines allow for prognostic, diagnostic, geolocation, and remote monitoring to minimize machine downtime.

KOHLER KSD engines offer 2.000 hours of service interval of the Poly–V fan belt and no valve lash adjustment.

The service interval of up to 500 hours for both oil and fuel filters and a 3–year warranty providing up to 3000 hours of protection reduces the total cost of ownership, making KSD–powered applications extremely productive with increased uptime.

The indirect injection system does not affect the fuel consumption rate: on the contrary, the electronic management and the focus on clean combustion drive low oil and fuel consumption and avoid oil dilution as well as heavy soot oil contamination.

Turbo Common Rail Engines

Standard equipment

Intake manifold

armoid

Exhaust manifold

Side oil refilling

Electric starter

45A alternator

Backplate flange

7 1/2" flywheel

Oil filter engine mounted

+ oil cooler

Fuel filter engine mounted

ECU

Oil sump capacity 3.7 L

Basic J1939 enabled

Wiring Harness

Accessories on demand

Fly wheel housing:

· SAE 5 (6 ½")

· SAE 4 (7 ½")

Hydraulic pump provision

on 3rd PTO

Flexible fan position

High capacity

oil sump 5.3 L

Remote oil and fuel filter

80A or 100a alternator

Full Capacity Wiring Harness


Muffler

Radiator

Heavy duty air cleaner

Arctic Boost

(≤-26°C startability)



KSD 1403TCA

Turbo Common Rail with Aftercooler






QUICK SPECIFICATIONS	KSD 1403TCA	
CYLINDERS / FIE	3 / TURBO COMMON RAIL	
MAX POWER kW (HP) @ rpm	18.4 (24.7) @ 3000 US TIER 4 FINAL 18.9 (25.7) @ 3000 STAGE V*	
MAX TORQUE Nm @ rpm	12() @ 14()()	
EMISSION COMPLIANCE	I US TIER 4 FINAL / FILSTAGE V	




*Engine model with double emission compliance (Stage V/Tier 4 Final): 18.4 kW (24.7 hp) @ 3000 rpm

Data

Dimensions (mm)






Performance curves

ACCORDING TO ISO 14396

KSD 1403TCA - TURBO COMMON RAIL WITH AFTERCOOLER




MB – Torque curveNB – Power curve

Performances measured according to ISO 14396 without final intake and exhaust line. Actual engine performances may be affected by accessories (intake and exhaust line, charging, cooling fan, etc.), application, ambient operating conditions (temperature, humidity, and altitude) and other factors.

KSD 1403TC

Turbo Common Rail






QUICK SPECIFICATIONS	KSD 1403TC	
CYLINDERS / FIE	CYLINDERS / FIE 3 / TURBO COMMON RAIL	
MAX POWER kW (HP) @ rpm	18.4 (24.7) @ 3000 US TIER 4 FINAL 18.9 (25.7) @ 3000 STAGE V*	
MAX TORQUE Nm @ rpm 105 @ 1500		
EMISSION COMPLIANCE	EU STAGE V, US TIER 4 FINAL, CHINA IV, BHARAT TREM V/CEV V	




*Engine model with double emission compliance (Stage V/Tier 4 Final): 18.4 kW (24.7 hp) @ 3000 rpm

Data

Dimensions (mm)






Performance curves

ACCORDING TO ISO 14396

KSD 1403TC - TURBO COMMON RAIL



MB – Torque curveNB – Power curve

Performances measured according to ISO 14396 without final intake and exhaust line. Actual engine performances may be affected by accessories (intake and exhaust line, charging, cooling fan, etc.), application, ambient operating conditions (temperature, humidity, and altitude) and other factors.

Naturally Aspirated Engines

Standard equipment

Intake manifold

Oil filter engine mounted

Exhaust manifold

Fuel filter engine mounted

Side oil refilling

ECU

Electric starter

Oil sump capacity 3.7 L

45A alternator

Basic J1939 enabled Wiring

Harness

Backplate flange

7 1/2" flywheel

Accessories on demand

Fly wheel housing:

· SAE 5 (6 ½")

· SAE 4 (7 ½")

Hydraulic pump provision

Flexible fan position

High capacity oil sump 5.3 L

on 3rd PTO

Remote oil and fuel filter

80A or 100a alternator

Full Capacity Wiring Harness


Muffler

Radiator

Heavy duty air cleaner

Arctic Boost

(≤-26°C startability)



KSD 1403NA

Naturally Aspirated






QUICK SPECIFICATIONS	KSD 1403NA	
CYLINDERS / FIE	3 / COMMON RAIL	
MAX POWER kW (HP) @ rpm	18.4 (24.7) @ 3000 US TIER 4 FINAL 18.9 (25.7) @ 3000 STAGE V*	
MAX TORQUE Nm @ rpm	90 @ 1800	
EMISSION EU STAGE V, US TIER 4 FINAL, COMPLIANCE CHINA IV, BHARAT TREM V/CEV V		




*Engine model with double emission compliance (Stage V/Tier 4 Final): 18.4 kW (24.7 hp) @ 3000 rpm

Data

Dimensions (mm)






Performance curves

ACCORDING TO ISO 14396

KSD 1403NA - NATURALLY ASPIRATED



MB – Torque curve
NB – Power curve

Performances measured according to ISO 14396 without final intake and exhaust line. Actual engine performances may be affected by accessories (intake and exhaust line, charging, cooling fan, etc.), application, ambient operating conditions (temperature, humidity, and altitude) and other factors.

12

Turbo Common Rail Engines





MODEL		KSD 1403TCA	KSD 1403TC
	4 STROKE DIESEL WITH CYLINDER IN LINE	•	•
	LIQUID COOLING	•	•
	2 VALVES PER CYLINDER	•	•
ENGINE ODEGO	IN CRANKCASE CAMSHAFT, GEAR TRAIN DRIVEN	•	•
ENGINE SPECS	PUSHROD – ROCKER ARMS TIMING WITH HYDRAULIC TAPPETS	•	•
	CAST IRON CRANKCASE	•	•
	CAST IRON CYLINDER HEAD	•	•
	CLOSED CRANKCASE VENTILATION SYSTEM	•	•
	CYLINDER	3	3
	BORE (mm)	81	81
	STROKE (mm)	90	90
TECHNICAL FEATURES	ENGINE DISPL (cm³)	1391	1391
	INJECTION SYSTEM	IDI	IDI
	INJECTION EQUIPMENT	IDI COMMON RAIL	IDI COMMON RAIL
	AFTERCOOLER	•	-
	MAX POWER (ISO 14396) [kW(hp) @ rpm]	18.4 (24.7) @ 3000 US TIER 4 F 18.9 (25.7) @ 3000 STAGE V ¹	18.4 (24.7) @ 3000 US TIER 4 F 18.9 (25.7) @ 3000 STAGE V ¹
PERFORMANCE	MAX TORQUE (ISO 14396) (Nm @ rpm)	120 @ 1400	105 @ 1500
	LOW-END TORQUE (Nm @ 1000 rpm)	95	80
	EMISSION COMPLIANCE	EU STAGE V, US TIER 4 FINAL, CHINA IV, BHARAT TREM V/CEV V	
FUEL ECONOMY	BEST POINT (G/kWh)	242	245
TOLL LOCKOWT	MAX POWER (G/kWh @ 1800 rpm)	255	256
	UNAIDED (°C)	DOWN TO -15	DOWN TO -15
STARTABILITY	UNAIDED (°C) WITH ARCTIC BOOST	DOWN TO -26	DOWN TO -26
	AIDED (°C) [COOLANT HEATER]	BELOW –26	BELOW -26
	EN 590	•	•
	NO 1 DIESEL (US) – ASTM D 975-09 B – GRADE 1-D S 15	•	•
FUEL COMPATIBILITY	NO 2 DIESEL (US) – ASTM D 975-09 B – GRADE 2-D S 15	•	•
	ARCTIC EN 590/ASTM D 975-09 B (NO PETROLEUM ADDED)	•	•
	HIGH SULFUR FUEL < 2000 PPM *	•	•
	HVO - HYDROTREATED VEGETABLE OIL	•	•
SERVICE	OIL/FILTER CHANGE INTERVAL STD/SYNTHETIC (HR)	500–1000**	500-1000**
FEATURES	ALTERNATOR BELT REPLACEMENT	36 MTH	36 MTH
	COOLANT CHANGE	24 MTH	24 MTH
	OIL CONSUMPTION (% FUEL)	<0.05	<0.05
	H×L×W (FAN EXCLUDED) (mm) WEIGHT (kg)	600 X 482 X 445 126	600 X 482 X 445 127
	WEIGHT (kg)	OPTIONAL SINGLE SERVICE SIDE	OPTIONAL SINGLE SERVICE SIDE
PHYSICAL	DAILY SERVICE POINTS – POSITIONS	(SELECT SIDE)	(SELECT SIDE)
CHARACTERISTICS	AMBIENT OPERATING TEMPS (°C)	-40 TO + 50***	-40 TO + 50***
	GRADEABILITY-ALL ROUND (CONTINOUS) (Deg)	35	35
	GRADEABILITY-ALL ROUND (INTERMITTENT-1MIN) (Deg)	45	45
LUBRICATION	OIL TYPE	10W-40 API CI4	10W-40 API CI4
AUXILIARY PTOS (3 RD OPTIONAL)	MAX TORQUE (Nm)	40	40
	DRIVE RATIO	1:1 TIMES ENGINE SPEED	1:1 TIMES ENGINE SPEED
	PROVISION FOR A DOUBLE GR.2 TANDEM HYDRAULIC PUMP	•	•

Naturally Aspirated Engines



MODEL		KSD 1403NA	
	4 STROKE DIESEL WITH CYLINDER IN LINE	•	
	LIQUID COOLING	•	
	2 VALVES PER CYLINDER IN CRANKCASE CAMSHAFT,	•	
ENGINE SPECS	GEAR TRAIN DRIVEN	•	
ENGINE SPECS	PUSHROD – ROCKER ARMS TIMING WITH HYDRAULIC TAPPETS	•	
	CAST IRON CRANKCASE	•	
	CAST IRON CYLINDER HEAD	•	
	CLOSED CRANKCASE VENTILATION SYSTEM	•	
	CYLINDER	3	
	BORE (mm)	81	
TECHNICAL	STROKE (mm)	90	
FEATURES	ENGINE DISPL (cm³)	1391	
	INJECTION SYSTEM	IDI	
	INJECTION EQUIPMENT	IDI COMMON RAIL	
	AFTERCOOLER	-	
	MAX POWER (ISO 14396) [kW(hp) @ rpm]	18.4 (24.7) @ 3000 US TIER 4 FINAL 18.9 (25.7) @ 3000 STAGE V¹	
PERFORMANCE	MAX TORQUE (ISO 14396) (Nm @ rpm)	90 @ 1800	
	LOW-END TORQUE (NM @ 1000 rpm)	70	
	EMISSION COMPLIANCE	EU STAGE V, US TIER 4 FINAL, CHINA IV, BHARAT TREM V/CEV V	
FUEL ECONOMY	BEST POINT (G/kWh)	243	
TOLL LCCHOWT	MAX POWER (G/kWh @ 2200 rpm)	253	
	UNAIDED (°C)	DOWN TO -15	
STARTABILITY	UNAIDED (°C) WITH ARCTIC BOOST	DOWN TO -26	
	AIDED (°C) [COOLANT HEATER]	BELOW –26	
	EN 590	•	
	NO 1 DIESEL (US) – ASTM D 975-09 B - GRADE 1-D S 15	•	
FUEL COMPATIBILITY	NO 2 DIESEL (US) – ASTM D 975-09 B – GRADE 2-D S 15	•	
COMPATIBILITY	ARCTIC EN 590/ASTM D 975-09 B (NO PETROLEUM ADDED)	•	
	HIGH SULFUR FUEL < 2000 PPM *	•	
	HVO - HYDROTREATED VEGETABLE OIL	•	
	OIL/FILTER CHANGE INTERVAL STD/SYNTHETIC (HR)	500-1000**	
SERVICE FEATURES	ALTERNATOR BELT REPLACEMENT	36 MTH	
	COOLANT CHANGE	24 MTH	
	OIL CONSUMPTION (% FUEL)	<0.05	
	H×L×W (FAN EXCLUDED) (mm)	552 X 482 X 418	
	WEIGHT (kg)	121 OPTIONAL SINGLE SERVICE SIDE	
PHYSICAL	DAILY SERVICE POINTS - POSITIONS	(SELECT SIDE)	
CHARACTERISTICS	AMBIENT OPERATING TEMPS (°C)	-40 TO +50***	
	GRADEABILITY-ALL ROUND (CONTINOUS) (Deg)	35	
	GRADEABILITY-ALL ROUND (INTERMITTENT-1MIN) (Deg)	45	
LUBRICATION	OIL TYPE	10W-40 API CI4	
AUXILIARY PTOS (3 RD OPTIONAL)	MAX TORQUE (Nm)	40	
	DRIVE RATIO	1:1 TIMES ENGINE SPEED	
	PROVISION FOR A DOUBLE GR.2 TANDEM HYDRAULIC PUMP	•	



 $\label{thm:contact} For more information, contact your Rehlko source of supply.$ Discovery Energy, LLC reserves the right to make modifications without prior notice.